



EXTRA LEGA PRODOTTI LUNGI IN ACCIAIO INOSSIDABILE

VALIDITA' : LUGLIO 2017

| CORRISPONDENZE | | | EURO/KG | | | |
|----------------------|------------------|-------|----------|-------|----------|-------------------|
| DESIGNAZIONE UNI | AISI | W.Nr. | BILLETTE | BARRE | VERGELLA | LAVORATI A FREDDO |
| X12C 13 | 410 | 4006 | 0,56 | 0,61 | 0,58 | 0,69 |
| X12C 13 | (410OG) | 4006 | 0,58 | 0,63 | 0,61 | 0,71 |
| X12CrS13 | 416 | 4005 | 0,59 | 0,64 | 0,62 | 0,72 |
| X20Cr13 | 420A | 4021 | 0,56 | 0,61 | 0,58 | 0,69 |
| X30Cr13 | 420B | 4028 | 0,56 | 0,61 | 0,58 | 0,69 |
| X29CrS13 | 420BF | 4029 | 0,59 | 0,64 | 0,62 | 0,72 |
| X4CrS13 | 420CF | 4035 | 0,59 | 0,64 | 0,62 | 0,72 |
| X40Cr14 | 420C | 4034 | 0,56 | 0,61 | 0,58 | 0,69 |
| X39CrMo17-1 | (420RM) | 4122 | 0,81 | 0,88 | 0,85 | 1,00 |
| X16CrNi 16 | 431 | 4057 | 0,77 | 0,84 | 0,80 | 0,94 |
| X90CrMoV18 | 440B | 4112 | 0,82 | 0,89 | 0,86 | 1,01 |
| X105CrMo17 | 440C | 4125 | 0,73 | 0,80 | 0,77 | 0,90 |
| X6CrTi12 | 409 | 4512 | 0,59 | 0,65 | 0,62 | 0,73 |
| X8Cr17 | 430 | 4016 | 0,68 | 0,74 | 0,71 | 0,84 |
| X10CrS 7 | 430F | 4104 | 0,71 | 0,77 | 0,74 | 0,87 |
| X3CrNb17 | 430NB | 4511 | 0,75 | 0,82 | 0,79 | 0,93 |
| X3CrTi17 | 430T | 4510 | 0,68 | 0,74 | 0,71 | 0,84 |
| X8CrMo17 | 434 / 430FMo | 4113 | 0,81 | 0,88 | 0,84 | 0,99 |
| X6CrMoS19-2 | | 4114 | 0,95 | 1,04 | 1,00 | 1,17 |
| X2CrNi18-11 | 304 L | 4306 | 1,28 | 1,40 | 1,34 | 1,57 |
| X5CrNi18-10 | 304 | 4301 | 1,17 | 1,28 | 1,23 | 1,44 |
| X10CrNi18-09 | 302 | 4310 | 1,14 | 1,24 | 1,19 | 1,40 |
| | 302Mo | | 1,16 | 1,27 | 1,22 | 1,43 |
| X10CrNiS18-09 | 303 | 4305 | 1,17 | 1,28 | 1,23 | 1,44 |
| X8CrNi18-12 | 305 | 4303 | 1,35 | 1,47 | 1,41 | 1,66 |
| X6CrNiTi18-10 | 321 | 4541 | 1,27 | 1,39 | 1,33 | 1,56 |
| X6CrNiNb18-11 | 347 | 4550 | 1,38 | 1,50 | 1,44 | 1,69 |
| X5CrNiNb19-9 | | 4551 | 1,35 | 1,47 | 1,41 | 1,65 |
| | 350 (XM-19) | | 1,77 | 1,93 | 1,85 | 2,17 |
| X1CrNiMoCuN20-18-7 | 354 (F44) | 4547 | 2,55 | 2,78 | 2,67 | 3,13 |
| X3CrNiCu19-9-2 | 304RH | 4560 | 1,23 | 1,34 | 1,29 | 1,51 |
| X3CrNiCu18-9-4 | 304K | 4567 | 1,30 | 1,42 | 1,36 | 1,60 |
| X6CrNiCuS18-9-2 | 303K | 4570 | 1,22 | 1,33 | 1,27 | 1,50 |
| X5CrNiMo17-12 | 316 | 4401 | 1,62 | 1,76 | 1,69 | 1,99 |
| X2CrNiMo17-12 | 316L | 4404 | 1,62 | 1,76 | 1,69 | 1,99 |
| X6CrNiMoTi1712-2 | 316Ti | 4571 | 1,65 | 1,79 | 1,72 | 2,02 |
| X5CrNiMoNb19-12 | 318Z | 4576 | 1,77 | 1,93 | 1,85 | 2,17 |
| X3CrNiCuMo17-11-3-2 | 316K | 4578 | 1,70 | 1,85 | 1,78 | 2,08 |
| X2CrNiMoCuS17-10-2 | 316LK | 4598 | 1,69 | 1,84 | 1,76 | 2,07 |
| X2CrNiMo19- 12 | 316LSi | 4430 | 1,67 | 1,82 | 1,74 | 2,05 |
| | E316LF | | 1,80 | 1,96 | 1,88 | 2,21 |
| X2 CrNiMo17-13 | 316LM | 4435 | 1,78 | 1,94 | 1,86 | 2,18 |
| X5 CrNiMo17-13 | 316M | 4436 | 1,72 | 1,88 | 1,80 | 2,11 |
| X2CrNiMo18-15-3 | | 4441 | 1,85 | 2,02 | 1,93 | 2,27 |
| X1CrNi19-9 | 308LSi | 4316 | 1,32 | 1,44 | 1,38 | 1,62 |
| | E308LF | | 1,41 | 1,54 | 1,47 | 1,73 |
| | 307 | | 1,15 | 1,25 | 1,20 | 1,41 |
| X8CrMnCuNb17-8-3 | 204Cu | 4597 | 0,93 | 1,01 | 0,97 | 1,14 |
| X10CrNi30-8 | E312 | 4337 | 1,50 | 1,64 | 1,57 | 1,84 |
| X2CrNiMo18-16 | 317L | 4438 | 1,94 | 2,12 | 2,03 | 2,38 |
| X12CrNi23-13 | 309 | 4833 | 1,51 | 1,65 | 1,58 | 1,85 |
| X2CrNi24-12 | 309S | 4332 | 1,52 | 1,66 | 1,59 | 1,87 |
| X15CrNiSi20-12 | | 4828 | 1,44 | 1,57 | 1,50 | 1,77 |
| X12CrNi22-12 | | 4829 | 1,38 | 1,51 | 1,44 | 1,69 |
| X12CrNi25-20 | 310 | 4845 | 1,97 | 2,15 | 2,06 | 2,42 |
| X12CrNi25-20 | 310S | 4842 | 1,97 | 2,15 | 2,06 | 2,42 |
| X15CrNiSi25-20 | 314 | 4841 | 1,97 | 2,15 | 2,06 | 2,42 |
| X2CrNiN23-4 | 324 | 4362 | 1,11 | 1,21 | 1,16 | 1,36 |
| X3CrNiMoN27-5-2 | 329 | 4460 | 1,40 | 1,53 | 1,46 | 1,72 |
| X2CrNiMoN22-5-3 | 329A (F51) | 4462 | 1,49 | 1,63 | 1,56 | 1,83 |
| | E329 (F51 sald.) | | 1,65 | 1,80 | 1,72 | 2,02 |
| X1NiCrMoCu25 20 5 | 904L | 4539 | 2,70 | 2,95 | 2,82 | 3,32 |
| X3CrNiMo13-4 | S 41500 (F6NM) | 4313 | 0,86 | 0,93 | 0,89 | 1,05 |
| X4CrNiMo16-5-1 | (415M) | 4418 | 1,08 | 1,18 | 1,13 | 1,33 |
| X5CrNiCuNb16-5 | 630 | 4542 | 1,04 | 1,14 | 1,09 | 1,28 |
| X2CrNiMoCuWN25-7-4 | S 32760 (F55) | 4501 | 1,72 | 1,88 | 1,80 | 2,12 |
| X6NiCrTiMoVB25- 15-2 | 660 | 4980 | 2,35 | 2,57 | 2,46 | 2,89 |
| X12NiCrSi35-16 | 330 | 4864 | 2,61 | 2,84 | 2,72 | 3,20 |

N.B.: le corrispondenze non evidenziate in tabella devono essere concordate direttamente con i produttori.